

STOCK SPRING PRICE LIST

PRICE GROUP	PRICE EACH IN POUNDS STERLING			PRICE PER 100 IN POUNDS STERLING
	QUANTITIES			QUANTITIES
	1 - 19	20 - 49	50 - 99	100 - 199
A	1.37	0.82	0.60	41.90
B	1.44	0.85	0.63	43.60
C	1.53	0.92	0.67	46.90
D	1.59	0.99	0.72	50.40
E	1.69	1.01	0.75	51.67
F	1.76	1.05	0.77	53.58
G	1.86	1.08	0.79	55.38
H	1.93	1.13	0.82	57.50
J	2.04	1.20	0.88	60.80
K	2.13	1.25	0.93	63.55
L	2.25	1.35	0.99	68.86
M	2.38	1.44	1.04	73.42
N	2.52	1.53	1.13	78.51
P	2.73	1.66	1.22	83.92
Q	2.92	1.80	1.34	91.78
R	3.15	1.92	1.43	98.46
S	3.40	2.13	1.57	109.07
T	3.64	2.28	1.70	116.91
U	3.94	2.49	1.85	127.64
V	4.22	2.67	1.95	136.76
W	4.53	2.87	2.13	147.47
X	4.86	3.01	2.21	155.11
Y	5.23	3.50	2.60	180.16
Z	5.62	3.68	2.73	188.53
BA	5.92	4.11	3.09	215.18
BB	6.31	4.33	3.20	226.37
BC	6.74	4.68	3.44	242.36
BD	7.16	4.95	3.66	258.35
BE	7.57	5.34	3.93	277.75
BF	7.99	5.58	4.15	291.94
BG	8.40	5.92	4.37	309.64
BH	8.79	6.23	4.60	325.52
BJ	9.51	6.71	4.93	349.19
BK	9.63	6.97	5.18	367.97
BL	10.54	7.48	5.50	390.98
BM	10.92	7.78	5.78	411.37
BN	11.52	8.13	6.04	427.46
BP	11.88	8.40	6.22	443.77
BQ	12.22	8.75	6.50	458.92
BR	12.58	8.97	6.69	474.15
BS	12.90	9.43	6.99	494.41
BT	13.25	9.98	7.36	519.59
BU	13.70	10.24	7.61	540.48
BV	14.04	10.69	7.92	561.48

STOCK SPRING PRICE LIST

	PRICE EACH IN POUNDS STERLING			PRICE PER 100 IN POUNDS STERLING
	QUANTITIES			QUANTITIES
PRICE GROUP	1 - 19	20 - 49	50 - 99	100 - 199
BW	14.44	10.79	8.07	573.75
BX	14.73	11.14	8.46	599.86
BY	15.17	11.63	8.72	619.16
BZ	15.87	12.05	9.02	643.36
CA	16.42	12.50	9.32	668.64
CB	17.24	13.04	9.81	698.60
CC	17.84	13.62	10.24	722.17
CD	18.71	14.11	10.67	757.24
CE	19.89	15.13	11.42	810.01
CF	21.21	16.16	12.18	863.11
CG	22.29	17.65	13.25	919.10
CH	23.27	18.46	13.78	978.81
CJ	24.19	19.17	14.38	1042.79
CK	25.11	19.86	14.92	1108.89
CL	26.09	20.68	15.51	1183.53
CM	27.08	21.44	16.05	1300.82
CN	28.17	22.29	16.75	1428.77
	PRICE EACH IN POUNDS STERLING			PRICE PER 100 IN POUNDS STERLING
	QUANTITIES			QUANTITIES
PRICE GROUP	1 - 19	20 - 49	50 - 99	100 - 199
AA	1.93	1.53	1.33	100.56
AB	2.38	1.89	1.64	124.81
AC	2.63	2.10	1.88	140.49
AD	3.10	2.51	2.24	168.40
AE	3.63	2.95	2.65	201.22
AF	4.30	3.59	3.20	242.41
AG	4.78	4.02	3.58	272.31
AH	5.44	4.54	4.12	305.75
AJ	5.69	4.97	4.52	337.54
AK	6.25	5.48	4.98	373.71
AL	6.90	5.98	5.44	406.74
AM	7.59	6.75	6.11	455.97
AN	8.65	7.61	6.94	528.00
AP	9.73	8.61	7.85	593.85
AQ	11.08	9.73	8.83	671.84
AR	12.44	10.99	10.04	755.88
AS	13.76	12.17	11.10	845.89
AT	15.54	13.72	12.43	947.91
AU	17.22	15.24	13.82	1061.95
AV	19.21	17.10	15.55	1187.60
AW	21.96	19.45	17.64	1360.91
AX	25.24	22.49	20.58	1580.55
AY	28.84	26.88	23.16	1894.98
AZ	33.43	31.14	26.66	2196.46

FOR QUANTITIES OF 1000 PIECES OR MORE PLEASE TELEPHONE

Call: +44 (0)118 978 1800 | Visit: www.leespring.co.uk | Fax: +44 (0)118 977 4832 | Email: sales@leespring.co.uk

STOCK SPRING PRICE LIST

PRICE GROUP	PRICE EACH IN POUNDS STERLING			PRICE PER 100 IN POUNDS STERLING
	QUANTITIES			QUANTITIES
	1 - 19	20 - 49	50 - 99	100 - 199
W1	3.86	2.29	1.19	69.48
W2	3.99	2.38	1.23	71.52
W3	4.19	2.52	1.30	75.61
W4	4.41	2.67	1.38	79.69
W5	4.65	2.87	1.47	87.87
W6	4.87	3.01	1.55	91.95
W7	5.14	3.20	1.66	98.08
W8	5.39	3.38	1.77	103.19
W9	5.65	3.55	1.87	110.34
W10	5.96	3.77	1.99	119.54
W11	6.24	3.96	2.13	126.69
W12	6.54	4.16	2.22	133.84
W13	6.87	4.36	2.36	144.06
W14	7.19	4.59	2.49	155.30
W15	7.55	4.82	2.65	166.54
W16	7.95	5.17	2.83	181.86
W17	8.34	5.43	3.02	193.10
W18	8.76	5.74	3.22	207.41
W19	9.19	6.06	3.40	229.88
W20	9.63	6.37	3.67	250.32
W21	10.14	6.73	4.01	273.82
W22	10.65	7.12	4.37	298.34
W23	11.18	7.52	4.70	323.88
W24	11.76	7.95	5.03	351.46
W25	12.35	8.44	5.29	372.92
W26	12.98	8.95	5.71	400.51
W27	13.63	9.79	6.05	424.01
W28	14.34	10.67	6.43	451.59
W29	15.07	11.30	6.94	484.29
W30	15.82	11.89	7.45	529.24
W31	16.60	12.50	7.97	563.98
W32	17.42	13.33	8.53	613.02
W33	18.30	14.04	9.15	671.26
W34	19.22	15.06	9.81	730.52
W35	20.20	16.13	10.50	774.45
W36	21.21	17.23	11.24	838.82
W37	22.28	18.28	12.04	896.03
W38	23.40	19.23	12.86	985.94
W39	24.57	20.30	13.76	1075.85
W40	25.81	21.94	14.71	1188.24

SPRING KIT PRICES IN POUNDS STERLING

SK 100	72.00	SK 300	134.00
SK 200	92.00	SK 301	156.00
SK 201	116.00	SK 350	40.00
SK 250	36.00	SK 351	43.00
SK 251	40.00	SK 800	61.00
		SK 801	65.00

HOW TO ORDER

**Free standard delivery
available within the UK**

Easy Ordering

Call: +44 (0)118 978 1800

Visit: leespring.co.uk

Email: sales@leespring.co.uk

Fax: +44 (0)118 977 4832

Convenient Payment Methods

Order using your Lee Spring account or Credit Card.



Free Shipping

Free shipping on all Stock Part(s) orders when the total part(s) value is more than £30 and delivered within the UK. Stock Part(s) orders with a parts value below £30 will be charged a freight and handling charge. Certificates of Conformity £10.00 per copy, per spring type.

Need Parts Fast?

Lee Spring offers expedited services to get you the springs you need when and where you want them. Lee Spring stocks a huge inventory of springs in stock and ready to ship.

Need a Quote?

Lee Spring can provide a stock or custom quote on the parts you need. Get up to the minute inventory information on all stock parts with just one call. Lee Spring pricing is available online 24/7 for quantities up to 1,000 pieces. For higher quantity, contact Lee Spring by calling +44 (0)118 978 1800, email sales@leespring.co.uk or fax +44 (0)118 977 4832.

Need Engineering or Technical Support?

Work directly with an experienced Lee Spring Engineer from design through production. Lee Spring has been manufacturing springs since 1918 and offers the highest quality technical support in the industry. Call +44 (0)118 978 1800 to speak directly with an engineer.

All prices are exclusive of VAT.

ORDER ONLINE @ leespring.co.uk

GUIDANCE ON PRICING

- 1** After selecting your stock springs from the catalogue refer to the column headed 'Price Group' and note the relevant letter(s) shown for the material required.
- 2** Using the price list, cross refer the price group letter(s) to the relevant quantity column and read off the price of your springs.
- 3** Prices for quantities greater than those covered on the price list are available on request.

More stock. More choice. More product lines.

Website

Stock spring catalogue

Custom spring design & manufacture

Convenient Online Ordering!

- ✓ Quickly Order Parts
- ✓ Find Pricing
- ✓ View Product Specification
- ✓ Download CAD Drawings
- ✓ Submit a Quote for Custom Springs and more!

Visit Lee Spring online today at leespring.co.uk

The screenshot shows the Lee Spring website interface. At the top, there is a navigation bar with links: About Us, Place an Order, Request a Quote, Request a Catalogue, Contact Us, Log In, Register. Below this is a grid of product categories: Compression Springs, LeeP Plastic Springs, REDUX™ Wave Springs, Die Springs, Extension Springs, Torsion Springs, Belleville Washers, and Speciality Parts/Constant Force. A 'Custom Springs' section is also visible. To the right, there is a 'The Lee Spring Difference' section with bullet points: Selection (23,000+ products), In Stock (ready to ship), Support (engineers ready to assist), and More Value (FREE grinding and CAD downloads). Below this is a 'Tips on How to Maximize Spring Life' link. Further right is the 'Lee Spring Knowledge Centre' with links to Custom Springs, Stock Springs, Spring-i-pedia, E-newsletters, Exhibition Schedule, Latest News, Blogs, Downloads (pdf), Series 20 Catalogue, REDUX™ Catalogue, Price List - £, Price List - Euros, ISO Certificates, Regulatory Compliance, and Technical Glossary. The footer contains ROHS COMPLIANT, ISO 9001 Registered Company, No.1 for Product, Service and Delivery, Conditions of Sale, Privacy Policy, Terms of Use, Tel: +44 (0)118 978 1800, Fax: +44 (0)118 977 4832, Email: sales@leespring.co.uk, and © Copyright 2016 Lee Spring Company.

PRICES ARE VALID UNTIL 31 DECEMBER 2018

Supersedes all previously published price lists



Lee Spring Limited, Latimer Road,
Wokingham, Berkshire, RG41 2WA, UK
Tel: +44 (0)118 978 1800
Fax: +44 (0)118 977 4832
sales@leespring.co.uk