

How To Determine

Free Standard Ground Shipping on Stock Springs for orders of \$40 or more in the Continental United States.

REDUX™ Wave Spring Pricing

PRICE GROUP	QUANTITIES				PRICE GROUP	QUANTITIES			
	1-19 Each	20-49 Each	50-99 Each	100-199 Each		1-19 Each	20-49 Each	50-99 Each	100-199 Each
P1	4.41	2.63	1.90	1.31	P13	11.25	7.09	5.05	3.55
P2	4.71	3.04	2.17	1.50	P14	11.71	7.40	5.25	3.71
P3	5.00	3.22	2.29	1.62	P15	12.17	7.62	5.43	3.76
P4	5.64	3.64	2.57	1.81	P16	12.71	8.03	5.70	3.94
P5	6.17	3.95	2.83	2.00	P17	13.11	8.28	5.88	4.07
P6	6.45	4.06	2.89	2.04	P18	14.04	8.87	6.31	4.36
P7	7.03	4.50	3.20	2.26	P19	14.63	9.25	6.57	4.55
P8	8.10	5.26	3.77	2.62	P20	15.79	9.96	7.08	4.90
P9	8.38	5.47	3.89	2.74	P21	16.96	10.70	7.61	5.25
P10	9.14	5.96	4.25	2.99	P22	19.53	12.31	8.75	6.05
P11	9.49	6.16	4.38	3.09	P23	21.56	13.60	9.67	6.69
P12	10.48	6.57	4.69	3.28	P24	22.79	14.38	10.21	7.05

Belleville Spring Washers Pricing

W1	6.78	4.04	2.11	1.23	W21	17.77	11.80	7.03	4.84
W2	7.01	4.19	2.20	1.27	W22	18.68	12.51	7.69	5.24
W3	7.36	4.44	2.30	1.35	W23	19.61	13.21	8.26	5.70
W4	7.76	4.70	2.44	1.43	W24	20.63	13.95	8.82	6.20
W5	8.16	5.06	2.59	1.57	W25	21.65	14.81	9.30	6.55
W6	8.56	5.31	2.74	1.65	W26	22.75	15.68	10.03	7.03
W7	9.03	5.62	2.93	1.74	W27	23.89	17.18	10.63	7.45
W8	9.47	5.95	3.12	1.84	W28	25.14	18.70	11.28	7.94
W9	9.93	6.26	3.29	1.97	W29	26.40	19.82	12.16	8.51
W10	10.45	6.64	3.53	2.14	W30	27.73	20.85	13.07	9.31
W11	10.97	6.97	3.75	2.25	W31	29.10	21.92	13.99	9.92
W12	11.46	7.32	3.92	2.37	W32	30.52	23.37	14.97	10.77
W13	12.05	7.69	4.16	2.54	W33	32.06	24.60	16.05	11.77
W14	12.62	8.08	4.40	2.74	W34	33.67	26.38	17.19	12.81
W15	13.26	8.47	4.67	2.94	W35	35.38	28.29	18.42	13.57
W16	13.94	9.09	4.97	3.21	W36	37.16	30.18	19.72	14.72
W17	14.63	9.54	5.31	3.40	W37	39.05	32.02	21.11	15.69
W18	15.38	10.07	5.66	3.67	W38	40.98	33.69	22.56	17.28
W19	16.12	10.65	5.99	4.05	W39	43.04	35.58	24.13	18.88
W20	16.92	11.19	6.45	4.42	W40	45.22	38.44	25.80	20.81

LeeP™ Plastic Composite Spring Pricing

L1	11.23	9.00	7.64	6.89	L4	14.17	11.35	9.65	8.67
L2	12.12	9.71	8.27	7.44	L5	15.33	12.25	10.42	9.39
L3	13.11	10.49	8.93	8.05					

* Type 302 may be substituted with Type 304 at Lee Spring's discretion. † Elgiloy is a trademark of Elgiloy Ltd. Partnership.

Termine Sales Prices

States.

FREE SHIPPING
on orders of
\$40
or more

1. Select the spring you want by **LEE STOCK NUMBER**.
2. Read across to the last column **PRICE GROUP** to obtain the price code letter under either column **M** (Music Wire), column **S** (302* Stainless Steel), or column **S316** (316 Stainless Steel), or column **E** (Elgiloy®) where applicable.
3. Refer to the **PRICE GROUP** below for quantities up to 199 pieces of an item.
4. For pricing on HEFTY™ Die Springs and Constant Force Springs, refer to their specific product sections.
5. Prices are subject to change without notice. For pricing from 200 to 1000 pieces, or to place an order online, visit www.leespring.com. For pricing above 1000 pieces, submit a request online at www.leespring.com, call 888-777-4647, email sales@leespring.com, or fax a request to 888-426-6655.

MAJOR CREDIT CARDS GLADLY ACCEPTED.



PRICES EFFECTIVE JANUARY 2021 • TERMS NET 30 DAYS.

Prices Shown are Per Spring Per Quantity.

Quantities Cannot Be Combined to Lower Item Pricing.

FREE GROUND SHIPPING AVAILABLE ON ORDERS OF \$40 OR MORE IN THE CONTINENTAL UNITED STATES.

Stock Parts orders with a parts value below \$40.00 with delivery within the Continental United States will be charged freight, plus a \$20.00 handling charge. Stock Parts orders with delivery outside the Continental United States with a parts value more than \$40.00 will pay freight only and no handling charge.

PRICE GROUP	QUANTITIES				PRICE GROUP	QUANTITIES			
	1-19 Each	20-49 Each	50-99 Each	100-199 Each		1-19 Each	20-49 Each	50-99 Each	100-199 Each
E	6.51	3.75	1.91	1.22	AS	17.81	11.22	7.38	5.33
F	6.82	3.92	2.03	1.24	AT	18.31	11.58	7.71	5.61
G	7.04	4.07	2.11	1.29	AU	18.81	11.98	8.07	5.90
J	7.26	4.18	2.20	1.37	AW	19.34	12.39	8.42	6.23
K	7.52	4.34	2.29	1.43	AX	19.90	12.80	8.82	6.54
L	7.81	4.53	2.40	1.51	AY	20.47	13.26	9.27	6.89
M	8.11	4.70	2.50	1.59	AZ	21.05	13.69	9.69	7.28
N	8.37	4.87	2.59	1.65	AZA	22.74	14.83	10.17	7.69
P	8.66	5.06	2.74	1.73	AZB	23.40	15.37	10.69	8.13
R	8.98	5.22	2.85	1.82	AZC	24.08	15.93	11.24	8.57
S	9.26	5.43	2.97	1.90	AZD	24.78	16.51	11.80	9.10
T	9.57	5.62	3.10	1.98	AZE	25.49	17.12	12.45	9.63
U	9.88	5.83	3.22	2.10	AZF	26.22	17.77	13.11	10.20
W	10.26	6.06	3.38	2.22	AZG	27.01	18.44	13.86	10.85
X	10.69	6.32	3.58	2.35	AZH	27.79	19.18	14.62	11.54
Y	11.02	6.54	3.72	2.45	AZJ	28.61	19.93	15.45	12.28
Z	11.36	6.76	3.86	2.55	AZK	29.45	20.75	16.33	13.10
AA	11.70	6.98	4.02	2.66	AZL	30.34	21.60	17.34	13.97
AB	12.04	7.20	4.18	2.81	AZM	31.82	22.61	18.38	14.92
AC	12.41	7.43	4.34	2.95	AZN	32.78	23.57	19.58	15.99
AD	12.75	7.69	4.55	3.07	AZO	33.75	24.61	20.81	17.15
AE	13.11	7.93	4.72	3.22	AZP	34.72	25.73	22.19	18.42
AG	13.51	8.20	4.92	3.36	AZQ	35.76	26.89	23.69	19.81
AJ	14.27	8.67	5.26	3.64	AZR	36.75	28.11	25.37	21.32
AK	14.68	8.99	5.51	3.81	AZS	37.82	29.64	27.16	23.04
AL	15.10	9.27	5.71	3.99	AZT	39.94	31.94	29.35	25.19
AM	15.51	9.56	5.96	4.18	AZU	42.48	34.84	32.08	27.66
AN	15.96	9.87	6.25	4.39	AZW	44.17	37.11	34.24	29.61
AO	16.39	10.18	6.48	4.60	AZX	45.93	39.50	36.50	31.68
AP	16.86	10.51	6.78	4.85	AZY	47.37	41.69	38.56	33.60
AR	17.32	10.86	7.05	5.07	AZZ	49.13	44.22	40.96	35.80

When ordering, please specify suffix **M** for Music Wire, **S** for 302 Stainless Steel*, **S316** for 316 Stainless Steel or **E** for Elgiloy, where applicable.