

How To Determine

Free Standard Ground Shipping on Stock Springs for orders of \$40 or more in the Continental United States.

REDUX™ Wave Spring Pricing

PRICE GROUP	QUANTITIES				PRICE GROUP	QUANTITIES			
	1-19 Each	20-49 Each	50-99 Each	100-199 Each		1-19 Each	20-49 Each	50-99 Each	100-199 Each
P1	4.74	2.96	2.14	1.48	P13	12.10	7.99	5.70	4.00
P2	5.06	3.43	2.44	1.69	P14	12.60	8.35	5.93	4.19
P3	5.38	3.63	2.58	1.83	P15	13.10	8.60	6.12	4.24
P4	6.07	4.11	2.90	2.04	P16	13.67	9.05	6.42	4.44
P5	6.64	4.46	3.19	2.26	P17	14.10	9.34	6.63	4.59
P6	6.94	4.58	3.26	2.30	P18	15.10	10.00	7.12	4.92
P7	7.57	5.07	3.61	2.55	P19	15.74	10.44	7.41	5.14
P8	8.71	5.94	4.25	2.95	P20	16.99	11.24	7.98	5.53
P9	9.01	6.16	4.39	3.09	P21	18.24	12.07	8.59	5.93
P10	9.83	6.73	4.79	3.37	P22	21.01	13.89	9.86	6.82
P11	10.21	6.94	4.94	3.48	P23	23.19	15.34	10.90	7.55
P12	11.28	7.41	5.29	3.70	P24	24.52	16.22	11.52	7.95

Belleville Spring Washers Pricing

W1	7.29	4.56	2.38	1.39	W21	18.47	13.3	17.93	5.46
W2	7.55	4.73	2.48	1.43	W22	19.42	14.11	8.67	5.91
W3	7.65	5.01	2.59	1.52	W23	20.38	14.90	9.32	6.43
W4	8.07	5.30	2.75	1.61	W24	21.44	15.73	9.95	6.99
W5	8.48	5.71	2.92	1.77	W25	22.51	16.70	10.49	7.39
W6	8.90	5.99	3.09	1.86	W26	23.65	17.68	11.31	7.93
W7	9.39	6.34	3.30	1.96	W27	24.83	19.38	11.99	8.40
W8	9.84	6.71	3.52	2.08	W28	26.13	21.09	12.72	8.96
W9	10.32	7.06	3.71	2.22	W29	27.44	22.35	13.71	9.60
W10	10.86	7.49	3.98	2.41	W30	28.83	23.52	14.74	10.50
W11	11.40	7.86	4.23	2.54	W31	30.25	24.72	15.78	11.19
W12	11.91	8.26	4.42	2.67	W32	31.73	26.36	16.88	12.15
W13	12.53	8.67	4.69	2.86	W33	33.33	27.75	18.10	13.27
W14	13.12	9.11	4.96	3.09	W34	35.00	29.75	19.39	14.45
W15	13.78	9.55	5.27	3.32	W35	36.78	31.91	20.78	15.31
W16	14.49	10.25	5.61	3.62	W36	38.63	34.04	22.24	16.60
W17	15.21	10.76	5.99	3.83	W37	40.59	36.11	23.81	17.70
W18	15.99	11.36	6.38	4.14	W38	42.60	38.00	25.44	19.49
W19	16.76	12.01	6.76	4.57	W39	44.74	40.13	27.22	21.29
W20	17.59	12.62	7.27	4.99	W40	47.01	43.35	29.10	23.47

LeeP™ Plastic Composite Spring Pricing

L1	12.08	10.16	8.62	7.78	L4	15.25	12.80	10.88	9.78
L2	13.04	10.96	9.32	8.39	L5	16.50	13.81	11.76	10.59
L3	14.11	11.83	10.07	9.08					

* Type 302 may be substituted with Type 304 at Lee Spring's discretion. † Elgiloy is a trademark of Elgiloy Ltd. Partnership.

Termine Sales Prices

FREE SHIPPING
on orders of
\$40
or more

1. Select the spring you want by LEE STOCK NUMBER.
2. Read across to the last column PRICE GROUP to obtain the price code letter under either column M (Music Wire), column S (302* Stainless Steel), or column S316 (316 Stainless Steel), or column E (Elgiloy®) where applicable.
3. Refer to the PRICE GROUP below for quantities up to 199 pieces of an item.
4. For pricing on HEFTY™ Die Springs and Constant Force Springs, refer to their specific product sections.
5. Prices are subject to change without notice. For pricing from 200 to 1000 pieces, or to place an order online, visit www.leespring.com. For pricing above 1000 pieces, submit a request online at www.leespring.com, call 888-777-4647, email sales@leespring.com, or fax a request to 888-426-6655.

MAJOR CREDIT CARDS GLADLY ACCEPTED.



PRICES EFFECTIVE JANUARY 2023 • TERMS NET 30 DAYS.

Prices Shown are Per Spring Per Quantity.

Quantities Cannot Be Combined to Lower Item Pricing.

FREE GROUND SHIPPING AVAILABLE ON ORDERS OF \$40 OR MORE IN THE CONTINENTAL UNITED STATES.

Stock Parts orders with a parts value below \$40.00 with delivery within the Continental United States will be charged freight, plus a \$20.00 handling charge. Stock Parts orders with delivery outside the Continental United States with a parts value more than \$40.00 will pay freight only and no handling charge.

PRICE GROUP	QUANTITIES			
	1-19 Each	20-49 Each	50-99 Each	100-199 Each
E	7.01	4.23	2.15	1.38
F	7.34	4.42	2.29	1.40
G	7.58	4.59	2.38	1.45
J	7.81	4.72	2.48	1.55
K	8.09	4.90	2.58	1.61
L	8.40	5.11	2.70	1.70
M	8.72	5.30	2.82	1.80
N	9.00	5.49	2.92	1.86
P	9.32	5.71	3.09	1.95
R	9.66	5.88	3.21	2.05
S	9.96	6.12	3.35	2.14
T	10.29	6.34	3.49	2.24
U	10.63	6.58	3.63	2.37
W	11.04	6.84	3.81	2.51
X	11.50	7.13	4.03	2.65
Y	11.86	7.38	4.20	2.77
Z	12.22	7.62	4.35	2.88
AA	12.59	7.87	4.53	3.00
AB	12.95	8.12	4.72	3.17
AC	13.35	8.38	4.90	3.33
AD	13.72	8.67	5.14	3.46
AE	14.11	8.94	5.32	3.63
AG	14.53	9.25	5.55	3.79
AJ	15.35	9.78	5.94	4.11
AK	15.79	10.14	6.22	4.29
AL	16.25	10.46	6.44	4.50
AM	16.68	10.78	6.73	4.72
AN	17.17	11.13	7.05	4.95
AO	17.64	11.49	7.31	5.19
AP	18.14	11.85	7.65	5.47
AR	18.64	12.25	7.95	5.72

PRICE GROUP	QUANTITIES			
	1-19 Each	20-49 Each	50-99 Each	100-199 Each
AS	19.16	12.65	8.33	6.01
AT	19.70	13.06	8.70	6.33
AU	20.24	13.51	9.11	6.65
AW	20.81	13.97	9.50	7.03
AX	21.41	14.44	9.95	7.38
AY	22.03	14.96	10.46	7.78
AZ	22.65	15.44	10.93	8.21
AZA	24.47	16.73	11.47	8.67
AZB	25.18	17.34	12.06	9.17
AZC	25.90	17.96	12.68	9.67
AZD	26.66	18.62	13.31	10.26
AZE	27.42	19.31	14.04	10.86
AZF	28.21	20.04	14.78	11.51
AZG	29.06	20.80	15.63	12.24
AZH	29.90	21.63	16.49	13.02
AZJ	30.78	22.47	17.42	13.85
AZK	31.68	23.40	18.42	14.77
AZL	32.64	24.37	19.55	15.76
AZM	34.23	25.50	20.73	16.83
AZN	35.27	26.58	22.08	18.04
AZO	36.31	27.75	23.47	19.35
AZP	37.36	29.02	25.03	20.78
AZQ	38.47	30.33	26.72	22.34
AZR	39.54	31.70	28.62	24.04
AZS	40.69	33.43	30.63	25.99
AZT	42.97	36.02	33.10	28.41
AZU	45.71	39.29	36.18	31.20
AZW	47.53	41.85	38.62	33.40
AZX	49.42	44.55	41.16	35.73
AZY	50.97	47.02	43.49	37.90
AZZ	52.86	49.88	46.20	40.37

When ordering, please specify suffix **M** for Music Wire, **S** for 302 Stainless Steel*, **S316** for 316 Stainless Steel or **E** for Elgiloy, where applicable.