

STOCK SPRINGS

YOU NEED IT. WE HAVE IT.

Compression Springs



Free Length	0.039-39.961in
# of Parts	16,006

Extension Springs



Free Length	0.250-11.417in
Outside Diameter	0.063-2.000in
# of Parts	5,399

Torsion Springs



Outside Diameter	0.103-2.141in
Work Over Rod	0.059-1.656in
Length of Leg	0.375-4.250in
# of Parts	2,442

LeeP™ Springs



Free Length	0.375-1.25in
Material	Ultem Plastic Composite
# of Parts	38

REDUX™ Wave Springs



Outside Diameter	0.210-1.707in
Free Height	0.060-2.000in
# of Parts	732

HEFTY™ Die Springs



Free Length	1-12in
# of Parts	490

Belleville Washers



Outside Diameter	0.188-9.843in
Inside Diameter	0.093-5.000in
# of Parts	536

Battery Springs



AAA, AA, C and D Battery Sizes	Various Mount Types
# of Parts	32

Continuous Length



12", 24", and 36" Lengths	
# of Parts	270

Constant Force Springs



Load Range	0.230-16.500lb
Material Width	0.250-1.250in
# of Parts	40

Drawbar Springs



8.30" Length Available in Medium or High Load	
# of Parts	4

Spring Guides



Round and flat wire designs with stock lengths up to 12 feet	
# of Parts	248



You Need It, We Have It!
Visit leespring.com

25,000+
Stock
Springs

Custom Spring Type Designs

Compression Spring	Outside Diameter: 0.010" – 5.75"/0.25 mm – 146.1 mm Wire Diameter: 0.002" – 0.625"/0.05 mm – 15.88 mm
Extension Spring	Outside Diameter: 0.010" – 5.75"/0.25 mm – 146.1 mm Wire Diameter: 0.002" – 0.625"/0.05 mm – 15.88 mm
Torsion Spring	Outside Diameter: 0.010" – 5.75"/0.25 mm – 146.1 mm Wire Diameter: 0.002" – 0.625"/0.05 mm – 15.88 mm
Wave Spring	Outside Diameter: 0.210" – 5.000"/5.33 mm – 127.0 mm Inside Diameter: 0.150" – 4.54"/3.81 mm – 115.32 mm
Constant Force	Min. Outside Diameter: 0.340"/8.636 mm Min Length: 11.80"/299.72 mm Inside Diameter: 0.280" – 1.97"/7.11 mm – 50.04 mm
Wire Forms	Wire Diameters: 0.010" – 0.24" /0.25 mm – 6 mm Maximum Finished Length: 60"/ 1524 mm
Stampings	Strip Width: up to 3" / 76.20 mm Strip Thickness: 0.005 to 0.062" /0.13mm – 1.57 mm
Fourslide Parts	Strip Width: 0.010" – 0.500"/0.25 mm – 12.70 mm Strip Thickness: 0.003" – 0.125"/ 0.08 mm – 3.18 mm Wire Diameter: 0.005" – 0.187"/ 0.13 mm – 4.75 mm

Materials

Beryllium Copper
Brass
Carbon Steel, Hard Drawn
Carbon Steel, Oil Tempered
Chrome Silicon, Oil Tempered
Chrome Vanadium, Oil Tempered
Elgiloy®
Hastelloy®***

Inconel®
Monel®
Music Wire
Phosphor Bronze
Plastic Composites
Stainless Steel, 300 Series
Stainless Steel, 17-7



Custom Spring Knowledge

Lee Spring offers a wide selection of custom spring capabilities, design and engineering support, extensive material options, and finish choices. Our experience combined with our custom spring manufacturing capabilities has made us a market leader in the design and manufacturing of custom springs.

Finishes and Services

Assembly
Color Coding
Electropolishing
Grinding
Heat Treating
Looping
Passivation
Powder Coating
Shot Peening
Spring Setting
Plating: Nickel, Zinc, Cadmium
Special Finishes (e.g., Black Oxide)



You Need It, We Have It!
Visit leespring.com



CUSTOM SPRINGS
YOU NEED IT.
WE HAVE IT.